



3D grain	orientation	mapping of	of polycr	ystals or	า scales f	rom 1	mm to 1	nm us	ing 3D-
XRD and		•							

Huang, Xiaoxu; Poulsen, Henning Friis; Schmidt, Søren; Godfrey, A.

Publication date:

Link back to DTU Orbit

Citation (APA):

Huang, X., Poulsen, H. F., Schmidt, S., & Godfrey, A. (2011). 3D grain orientation mapping of polycrystals on scales from 1 mm to 1 nm using 3D-XRD and TEM. Abstract from 13th International congress for Stereology, Beijing (CN), 19-23 Oct, .

## DTU Library

Technical Information Center of Denmark

## **General rights**

Copyright and moral rights for the publications made accessible in the public portal are retained by the authors and/or other copyright owners and it is a condition of accessing publications that users recognise and abide by the legal requirements associated with these rights.

- Users may download and print one copy of any publication from the public portal for the purpose of private study or research.
- You may not further distribute the material or use it for any profit-making activity or commercial gain
- You may freely distribute the URL identifying the publication in the public portal

If you believe that this document breaches copyright please contact us providing details, and we will remove access to the work immediately and investigate your claim.

## 3D grain orientation mapping of polycrystals on scales from 1 mm to 1 nm using 3D-XRD and TEM

X. Huang<sup>1,2</sup>, H.F. Poulsen<sup>2</sup>, S. Schmidt<sup>2</sup>, A. Godfrey<sup>3</sup>

- 1. Danish-Chinese Center for Nanometals, Materials Research Division, Risø DTU, 4000 Roskilde, Denmark.
- 2. Center for Metal Structures in Four Dimensions, Materials Research Division, Risø DTU, 4000 Roskilde, Denmark.
- 3. Department of Materials Science and Engineering, Tsinghua University, Beijing 100084, P.R. China.

Polycrystals are composed of millions of small crystals (grains). The orientations, shapes, sizes and relative arrangement of these grains are important in determining many material properties. Traditionally, it has only been possible to obtain information on these structural parameters by looking at a cut surface using two-dimensional characterization techniques, for example optical microscopy and electron microscopy. We have developed a set of techniques for three-dimensional (3D) grain orientation mapping of polycrystals and here we provide an overview of these techniques.

For millimetre size specimens the characterisation is based on diffraction by x-rays generated by a synchrotron source. The technique, Three-Dimensional X-Ray Diffraction (3DXRD) microscopy, allows several modes of operation, including grain morphology mapping and grain center mapping. In the grain morphology mapping mode, 3D grain maps with more than 1000 grains are made routinely, with a spatial resolution of 1-5  $\mu$ m. In the grain center mapping mode, each grain is characterized with respect to center-of-mass position, volume, and its average orientation. At present the positional accuracy is ~2  $\mu$ m.

Recently we have succeeded in developing a new technique, 3D Orientation Mapping in the Transmission Electron Microscope (3D-OMiTEM), for 3D grain orientation mapping in nanocrystalline materials that have grain sizes substantially smaller than the thickness of TEM foil specimens. The data collection is based on the concept of conical scanning dark field imaging; hence images are acquired over a wide range of beam tilts. In addition, to enable a 3D reconstruction of the grains, the acquisition procedure is repeated for many sample tilts. The reconstruction software is a variant of the algorithm originally developed for orientation mapping with 3DXRD.