

Engineering Conferences International ECI Digital Archives

Single-Use Technologies: Bridging Polymer Science
to Biotechnology Applications

Proceedings

Fall 10-20-2015

Robust, fast and accurate pH sensing platform solution targeting Single Use application

Srinivas Rao

Senova Systems Inc, srinivas.rao@senovasystems.com

Hardjinder Ladhar

Senova Systems Inc

Jai Krishnamurthy

Senova Systems Inc

Follow this and additional works at: <http://dc.engconfintl.org/biopoly>

 Part of the [Materials Science and Engineering Commons](#)

Recommended Citation

Srinivas Rao, Hardjinder Ladhar, and Jai Krishnamurthy, "Robust, fast and accurate pH sensing platform solution targeting Single Use application" in "Single-Use Technologies: Bridging Polymer Science to Biotechnology Applications", Ekta Mahajan, Genentech, Inc., USA Gary Lye, University College London, UK Eds, ECI Symposium Series, (2015). <http://dc.engconfintl.org/biopoly/55>

This Article is brought to you for free and open access by the Proceedings at ECI Digital Archives. It has been accepted for inclusion in Single-Use Technologies: Bridging Polymer Science to Biotechnology Applications by an authorized administrator of ECI Digital Archives. For more information, please contact franco@bepress.com.

Robust, fast and accurate pH sensing platform solution targeting Single Use Application

Srinivas Rao, Ph.D., Harjinder Ladhar, Ph.D., and Jai Krishnamurthy, Ph.D.

E-mail: Srinivas.Rao@SenovaSystems.com

Senova Systems, Inc.,

Abstract:

QbD in biotech and life-sciences necessitates good process metrics in drug discovery, development and manufacturing. Accurate knowledge of pH measurements remains fundamentally important. There is much to be desired with use of conventional glass potentiometric probes for monitoring pH. Challenges being measurement accuracy, system drift, and need for frequent calibration. Additionally glass being fragile compounds the situation further in manufacturing.

Glass probes for pH measurement are really unattractive for single use system applications (SUS). Optical based solutions while easy to integrate lack range, need calibration and are a problem in storage (application timing).

We demonstrate a robust Platform Solution tested for a variety of applications that includes environs demanding repeated use and SUS. The innovative solution deploys electrochemical based redox chemistry engineered to deliver a scalable (semiconductor technologies) non-glass, calibration-free, drift-free, robust sensing platform. The System Solution is flexible and simply packaged as a 2D 'sticker' easily molded into a bag or a 3D probe for insertion in typical 12mm ports in-place for glass probes.

Technical performance data will be presented indicating wide performance range (pH 3.0 – 12.0), accuracy (+/- 0.1), covering 5° C – 50° C, calibration-free (factory set, and stable), drift-free (over process duration greater than 35 days), ability to withstand Clean-In-Place (CIP), Steam-In-Place, and gamma irradiation expected of SUS as well as up-stream and down-stream applications.

The author will share experience driving six sigma methodologies in successful development of a pH sensing platform.