

Nanoscale 2016 vol.8 N47, pages 19867-19875

---

## Near-field Raman dichroism of azo-polymers exposed to nanoscale dc electrical and optical poling

Kharintsev S., Fishman A., Saikin S., Kazarian S.  
*Kazan Federal University, 420008, Kremlevskaya 18, Kazan, Russia*

---

### Abstract

© 2016 The Royal Society of Chemistry. Azobenzene-functionalized polymer films are functional materials, where the (planar vs. homeotropic) orientation of azo-dyes can be used for storing data. In order to characterize the nanoscale 3D orientation of the pigments in sub-10 nm thick polymer films we use two complementary techniques: polarization-controlled tip-enhanced Raman scattering (TERS) microscopy and contact scanning capacity microscopy. We demonstrate that the homeotropic and planar orientations of the azo-dyes are produced by applying a local dc electrical field and a resonant longitudinal optical near-field, respectively. For a non-destructive probe of the azo-dye orientation we apply a non-resonant optical near-field and compare the intensities of the Raman-active vibrational modes. We show that near-field Raman dichroism, a characteristic similar to the absorption dichroism used in far-field optics, can be a quantitative indicator of the 3D molecular orientation of the azo-dye at the nanoscale. This study directly benefits the further development of photochromic near-field optical memory that can lead to ultrahigh density information storage.

<http://dx.doi.org/10.1039/c6nr07508h>

---