

Technical University of Denmark



ETEM characterization of NiGa model catalysts for CO₂ hydrogenation to Methanol

Spiga, Cristiano; Almind, Mads Radmer; Secher, Niklas Mørch; Silva, Hugo José Lopes; Gardini, Diego; Wagner, Jakob Birkedal; Chorkendorff, Ib; Damsgaard, Christian Danvad

Publication date:
2016

Document Version
Peer reviewed version

[Link back to DTU Orbit](#)

Citation (APA):
Spiga, C., Almind, M. R., Secher, N. M., Silva, H. J. L., Gardini, D., Wagner, J. B., ... Damsgaard, C. D. (2016). ETEM characterization of NiGa model catalysts for CO₂ hydrogenation to Methanol. Abstract from 4th International Symposium on Advanced Electron Microscopy for Catalysis, Berlin, Germany.

DTU Library
Technical Information Center of Denmark

General rights

Copyright and moral rights for the publications made accessible in the public portal are retained by the authors and/or other copyright owners and it is a condition of accessing publications that users recognise and abide by the legal requirements associated with these rights.

- Users may download and print one copy of any publication from the public portal for the purpose of private study or research.
- You may not further distribute the material or use it for any profit-making activity or commercial gain
- You may freely distribute the URL identifying the publication in the public portal

If you believe that this document breaches copyright please contact us providing details, and we will remove access to the work immediately and investigate your claim.

ETEM characterization of NiGa model catalysts for CO₂ hydrogenation to Methanol

Cristiano Spiga^{1,2}, Mads R. Almind^{1,2}, Niklas Secher^{1,2}, Hugo J.L. Silva², Diego Gardini¹, Jakob B. Wagner¹, Ib Chorkendorff², Christian D. Damsgaard^{1,2*}

¹ Center for Electron Nanoscopy, Technical University of Denmark, DK-2800 Kgs. Lyngby, Denmark

² Center for Individual Nanoparticle Functionality, Department of Physics, Technical University of Denmark, DK-2800 Kgs. Lyngby, Denmark

*: presenting author, email: Christian.Damsgaard@cen.dtu.dk

Metal nanoparticles (NPs) dispersed on a high surface area support are widely used as catalysts for heterogeneous catalysis. The atomic configuration of the active NPs is highly linked to the performance of the catalyst. An Environmental Transmission Electron Microscope (ETEM) equipped with a differential pumping system to confine a controlled gas flow around the specimen offers a unique tool to investigate individual NPs at the atomic level in a gaseous environment. However, the morphology of the high surface area support often complicates the interpretation of TEM micrographs on the atomic level and blurs the spectroscopic information due to limited depth of field multiple scattering events. One way to circumvent this is to synthesize NPs on a low surface area support representing the “real” high surface area supported catalyst.

δ -Ni₅Ga₃ catalysts prepared by incipient wetness impregnation on a high surface area SiO₂ support (Figure 1A), have shown promising for CO₂ hydrogenation to methanol with comparable turn-over frequencies to the preferred commercial Cu/Zn/Al₂O₃ catalyst system[1-2]. This study presents TEM investigations of NiGa NPs supported on 200 nm SiO₂ nano-spheres (Figure 1B) and 20 nm thick SiO₂ membranes (Figure 1C)[4], respectively.

By studying the morphology (surface structure, facets, NP size, crystal structure, material composition) of these model catalysts during synthesis and CO₂ hydrogenation to methanol, we aim to describe the catalyst formation process and the pre-dominant deactivation mechanism at the atomic level. Complementary observations have been acquired using *in-situ* X-Ray Diffraction (XRD) and catalytic activity measurements using a Gas Chromatograph (GC) or Mass Spectrometer (MS).

The nano-sphere supported model catalyst features numerous NPs that can be illuminated directly with the electron beam. This enables atomic resolved structural (HRTEM) and spectroscopic information (EELS) of the individual NPs and was used to characterize phase, and surface structure during CO₂ hydrogenation.

The membrane supported model catalyst features numerous NPs with similar size distribution as the high surface area supported catalyst. This enables investigations of changes in size distribution, facet formation, and NP orientation (HRTEM) during synthesis and CO₂ hydrogenation.




Figure 1. TEM micrographs of NiGa NPs supported on A) High surface area SiO₂ support B) 200 nm SiO₂ spheres, and C) SiO₂ membrane.

References

- 1) Studt, F., et al., Nature Chemistry 6(2014), p. 320.
- 2) Sharafutdinov, I., et al., Journal of Catalysis, 320(2014), p. 77.
- 3) Hansen, T.W., et al., Materials Science and Technology 11(2010), p. 1338.
- 4) Damsgaard, C.D., et al., Microscopy 63(2014), p. 397.