June 1965


Brief 65-10188

NASA TECH BRIEF



NASA Tech Briefs are issued by the Technology Utilization Division to summarize specific technical innovations derived from the space program. Copies are available to the public from the Clearinghouse for Federal Scientific and Technical Information, Springfield, Virginia, 22151.

Refractory Metal Shielding (Insulation) Increases Operating Range of Induction Furnace



The problem: The operating range of an induction furnace is partially determined by the degree to which escaping heat, in the form of radiation, can be contained. Ceramic oxide refractory materials insulate well to 3000°F. Multiple shielding with a composite of refractory metal and ceramic oxide is effective to about 4500°F but the ceramic component is susceptible to thermal shock and crystalline instability above that level. Effective thermal shielding is needed to operate induction furnaces at temperatures above 5500°F.

The solution: A thermal radiation shield consisting, alternately, of a sheet of refractory metal foil and a loosely packed mat of refractory metal fibers in a concentric pattern. This shielding contains the radiation

from the furnace until it approaches the melting temperature of the shielding material.

How it's done: Tungsten foil is alternated with a tungsten spacer. This spacer may be in the form of a loosely packed fibrous mat, fiber felt sheet, woven wire mesh, or corrugated foil. The foil and spacer lamination is then wound about the furnace to the desired thickness. The shielding is then banded on the outside with tungsten wire.

Notes:

1. This shielding is compact, lightweight, and simple to fabricate and, because of its low mass density, exhibits little thermal inertia, thereby permitting more rapid thermal cycling.

(continued overleaf)

This document was prepared under the sponsorship of the National Aeronautics and Space Administration. Neither the United States Government, nor NASA, nor any person acting on behalf of NASA: A. Makes any warranty or representation, express or implied, with respect to the accuracy, completeness, or usefulness of the information contained in this document, or that the use of any information, apparatus, method, or process disclosed in this document may not infringe privately-owned rights; or B. Assumes any liabilities with respect to the use of, or for damages resulting from the use of, any information, apparatus, method, or process disclosed in this document.

- 2. A tungsten foil-tungsten fiber mat composite was tested on a vacuum induction furnace and a temperature of 5850°F was reached. Tungsten melts at approximately 6100°F.
- 3. This shielding technique should be of interest to manufacturers and users of high temperature ovens, high temperature fluid lines, chemical reaction vessels, etc.
- 4. Inquiries concerning this invention may be directed to:

Technology Utilization Officer Lewis Research Center 21000 Brookpark Road Cleveland, Ohio, 44135 Reference: B65-10188 **Patent status:** NASA encourages the immediate commercial use of this invention. It is owned by NASA and inquiries about obtaining royalty-free rights for its commercial use may be made to NASA, Code AGP, Washington, D.C., 20546.

Source: Ben T. Ebihara (Lewis-202)

Category No. 02