

December 1970

Brief 70-10507

NASA TECH BRIEF



NASA Tech Briefs announce new technology derived from the U.S. space program. They are issued to encourage commercial application. Tech Briefs are available on a subscription basis from the National Technical Information Service, Springfield, Virginia 22151. Requests for individual copies or questions relating to the Tech Brief program may be directed to the Technology Utilization Division, NASA, Code UT, Washington, D.C. 20546.

Laser Wavelength Selector and Output Coupler

An optical system eliminates the displacement that occurs when wavelengths are selected in a multiple wavelength laser which utilizes intracavity wavelength selection by the first-order Littrow reflection of a plane grating. In such systems, some radia-

wavelength selection takes place about the line of intersection. The included angle need not be 90° ; in fact, the most useful configurations result for other angles. The ray path may form a delta, a Z, or a U.




Figure 1. Four Ray Paths

tion inevitably leaves the cavity through the zeroth order (specular) reflection of the grating. A simple, efficient output coupling can correct the problem by varying the direction of the output beam as different wavelengths are selected by grating rotation.

A plane mirror, or a plane-mirror extension, intersects the plane of the grating (Fig. 1). Rotation for

In the Z configuration, one external plane mirror makes the output beam collinear with the laser axis. Two laser cavities can then be coupled at a selectable, varying wavelength. If another coupling scheme is already in use, an external plane mirror perpendicular to the output beam can return the zeroth order loss to the cavity.

(continued overleaf)

Both input and output rays lie equidistant from the rotation axis. A given input ray and its two reflections lie tangent to the same circle, but different input rays lie tangent to different circles. Figure 2 shows one such construction. This system relies on mirror properties combined with the mirror-like grating response of the zeroth order.




Figure 2.

The technique was used to select and couple out a range of single wavelengths in a CO₂ laser. The system was pre-aligned with a visible laser. In a test using a helium-neon alignment laser, the carefully aligned CO₂ selector was rotated through an angle exceeding 10°. The output spot moved less than 1 mm at a distance of 7 m — 2500 times less than the uncorrected motion of the grating's zeroth order.

This optical system is simple and inexpensive to construct, and is easy to align. The optics are either fixed in space or rigidly attached to the rotating grating, and any optical wavelength can be used.

Applications include higher dispersion of unwanted wavelengths, for communications; efficient output coupling of a wide range of single wavelengths in the CO₂ laser; continuous wavelength tuning of or-

ganic dye lasers, while constant output beam position is maintained; and extracting the output of a variable angle-of-incidence reflectance spectrophotometer (sample replaces grating).

References:

1. Hard, Thomas M.: IEEE J. Quantum Electron., vol. QE-5, 1969, p. 321 (summary of paper presented at IEEE Conference on Laser Engineering Applications).
2. Hard, Thomas M.: Laser Wavelength Selection and Output Coupling by a Grating. Appl. Optics, vol. 9, Aug. 1970.

Note:

Requests for further information may be directed to:

Technology Utilization Officer
 Headquarters
 National Aeronautics
 and Space Administration
 Washington, D. C. 20546
 Reference: TSP70-10507

Patent status:

This invention is owned by NASA, and a patent application has been filed. Royalty-free, nonexclusive licenses for its commercial use will be granted by NASA. Inquiries concerning license rights should be made to:

Patent Counsel
 Mail Code 200-11A
 Ames Research Center
 Moffett Field, California 94035

Source: T. M. Hard
 Electronics Research Center
 (ERC-10248)